


3321 Multi-connecteur cylindrique corps femelle

Polymère technique, NBR




ØD	C	C1		Nombre de sorties	G	Kg
4	M46x1.5	M40x1.5	3321 04 00 04	4	55	0,065
	M46x1.5	M40x1.5	3321 04 00 07	7	55	0,063
	M65x1.5	M58x1.5	3321 04 00 12	12	75	0,125
6	M46x1.5	M40x1.5	3321 06 00 04	4	55	0,065
	M46x1.5	M40x1.5	3321 06 00 07	7	55	0,064

Le nombre de sorties de tubes du corps femelle doit correspondre à celui du corps mâle.

3329 Multi-connecteur cylindrique coiffe de protection


Polymère technique



C		Nombre de sorties	G	G1	L	Kg
M40x1.5	3329 00 02	4-7	35	50	55	0,062
M58x1.5	3329 00 03	12	34	70	70	0,139

3379 Bornier pour 2 tubes

Polymère technique, NBR




ØD		H	K	L	Kg
4	3379 04 00	34,5	11	39,5	0,010
6	3379 06 00	34,5	11	39,5	0,006
8	3379 08 00	46	13	44,5	0,008

Témoin de mise en pression de l'installation

3381 Bornier pour 3 tubes



Polymère technique, NBR



ØD		H	K	L	N	Kg
4	3381 04 00	36,5	11	39,5	11,5	0,013
6	3381 06 00	36,5	11	39,5	11,5	0,007
8	3381 08 00	46	13	44,5	14,5	0,033

Témoin de mise en pression de l'installation

Encombrement du multi-connecteur en traversée de cloison



Nombre de sorties de tube	L	ØD1
2	17	32,5
4-7	21	40,5
12	30,3	58,5