


3616 Union traversée de cloison égale


Laiton nickelé chimique FDA, FKM



ØD		F1	F2	K	L1	L2	ØT min	Kg
4	3616 04 00	13	14	14	14	20	12,5	0,018
6	3616 06 00	16	17	17,5	17	22	15	0,028
8	3616 08 00	18	19	19,5	18,5	23,5	17	0,036
10	3616 10 00	22	27	24	21,5	26,5	21	0,063
12	3616 12 00	24	24	26	23	27	23	0,062
14	3616 14 00	27	27	29,5	25,5	29,5	25	0,079

3636 Union traversée de cloison, femelle BSPP


Laiton nickelé chimique FDA, FKM



ØD	C		E	F1	F2	H	H1	K	ØT min	Kg
4	G1/8	3636 04 10	8,5	14	14	30,5	11	15	13	0,020
6	G1/8	3636 06 10	8,5	17	17	33	11	18,5	15	0,033
	G1/4	3636 06 13	11,5	17	17	37	15	18,5	15	0,033
8	G1/8	3636 08 10	8,5	19	19	34	10,5	21	17	0,044
	G1/4	3636 08 13	11,5	19	19	38	14,5	21	17	0,044
10	G3/8	3636 10 17	12	22	27	42,5	16	24	21	0,073
12	G3/8	3636 12 17	12	24	24	43	16	26	23	0,077
	G1/2	3636 12 21	16	27	24	48,5	21,5	29,5	23	0,133

3639 Équerre traversée de cloison égale

Laiton nickelé chimique FDA, FKM



ØD		F1	F2	G	H	K	L	ØT min	Kg
4	3639 04 00	13	14	10	35	14	18	12,5	0,023
6	3639 06 00	16	17	12	40,5	17,5	21,5	15	0,035
8	3639 08 00	18	19	15	44	19,5	23,5	17	0,046
10	3639 10 00	22	27	17,5	51	24	29	21	0,080
12	3639 12 00	24	24	19,5	55	26	31	23	0,086
14	3639 14 00	27	27	21,5	59	29,5	34	25	0,144

Raccord orientable.
Pression maximum = 20 bar